

# PSM1412-IC3A

**A low cost solution to your strapping needs.**

The PSM1412-IC3A is designed for general purpose semi automatic strapping. Although it is our lowest priced strapping machine, the low cost does not come at the expense of quality, consistency or reliability. Each PSM1412-IC3A comes with the exclusive PAC machine warranty, including on-line support for the life of the machine. We carry an extensive parts inventory and maintain over 99% parts availability within 24 hours. The PSM1412-IC3A has a convenient operators panel and externally controlled tension. In addition, all electronics are controlled with an integrated circuit control board to minimize down time and maintenance. Pricing on this unit is designed to expand the market to even the occasional user.



## **i** TECHNICAL SPECIFICATIONS

<b>Dimensions:</b>	35"L x 23"D x 30"H
<b>Package Size:</b>	Minimum - 3"W x 1"H Maximum - Unlimited
<b>Weight:</b>	190lbs.
<b>Tension Range:</b>	10 - 100 lbs.
<b>Speed:</b>	2.5 seconds per cycle
<b>Strap Size:</b>	1/4" - 5/8"
<b>Core Size:</b>	8x8 (additional 9x8 core is available)
<b>Power Requirements:</b>	110V, 50/60 Hz