



Main

Range of Product	9080G
Product Type	Terminal block
Localisation on Device	Standard
Color	Natural
Quantity	Set of 10

Complementary

Voltage Rating	600 V AC/DC
Current Rating	255 A UL 280 A CSA
Wire Size	AWG 6...250 kcmil aluminium/copper
Mounting Type	35 mm DIN rail 9080GH track
Certifications	CSA file 62144 class 6228 01 CE UL recognized E60616 CCN XCFR2
Electrical Connection	Tin plated aluminium box lugs
Material	Nylon block
Ambient air temperature for operation	-40...257 °F (-40...125 °C)
Electrical Connection Tightening Torque	Lug tin plated aluminium 225...250 lbf.in (25.42...28.25 N.m) : AWG 6...250 kcmil copper or aluminium)
Height	2.34 in (59.44 mm)
Width	3.32 in (84.33 mm)
Depth	1.17 in (29.72 mm)
Density	10 per foot

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	785901155072
Nbr. of units in pkg.	1
Package weight(Lbs)	4.32 oz (122.47 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.20 in (3.048 cm)
Package 1 width	2.20 in (5.588 cm)
Package 1 Length	3.30 in (8.382 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10

Package 2 Weight	2.81 lb(US) (1.275 kg)
Package 2 Height	2.40 in (6.096 cm)
Package 2 width	3.50 in (8.89 cm)
Package 2 Length	12.00 in (30.48 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------