

Product data sheet

Characteristics

9080GH112

Terminal block, Linergy, standard Square D mounting track, 12 inches long



Main

Range	9080G
Product	Standard Mounting Track
Quantity per Set	Set of 5

Complementary

Material	Galvanised sheet steel
Height	0.22 in (5.59 mm)
Width	0.81 in (20.57 mm)
Length	12 in (304.80 mm)

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	785901201861
Nbr. of units in pkg.	1
Package weight(Lbs)	1.92 oz (54.431 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.30 in (0.762 cm)
Package 1 width	0.90 in (2.286 cm)
Package 1 Length	12.00 in (30.48 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Weight	11.84 oz (335.658 g)
Package 2 Height	1.40 in (3.556 cm)
Package 2 width	1.40 in (3.556 cm)
Package 2 Length	12.20 in (30.988 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------