



Lineman's Pliers with Crimping, 9-Inch



These Lineman's Pliers feature a built-in crimper for non-insulated connectors. Heavy-duty cutting knives cut ACSR, screws, nails and most hardened wire. The high-leverage design provides 46-Percent more cutting power. The dual-material Journeyman handles are more comfortable and durable than other handles.

Specifications

Type:	Heavy Duty High Leverage Crimping Pliers	Application:	ACSR, Screws, Nails, Most Hardened Wire
Overall Length:	9.34" (23.7 cm)	Material:	Steel
Nose Type:	New England	Jaw Length:	1.594" (4 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.625" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Knife Length:	Light Blue
Joint Type:	Hot Riveted	Handle Color:	Light Blue
Handle Finish:	Plastic-Dipped	Handle Length:	5.375" (13.7 cm)
Insulated:	No	Tether Capable:	No
Weight:	1.1 lb (0.5 kg)		