



**MCR  
SAFETY**

# 34411 Luminator Drivers Specification Sheet

**PRODUCT DESCRIPTION:**

Pigskin gloves have excellent abrasion resistance. Offers greatest breathability because of the porous nature of the hide and becomes softer with use. Inherently retains natural softness after exposure to water. The 34411 features; premium grade black pigskin, Thermosock® lined, wing thumb, orange mesh back, lime and retro reflective material, knit wrist and shirred elastic back.

**FEATURES:**

- Black Grain Pigskin
- Orange Mesh Back with Lime Retro-Reflective Material
- Knit Wrist
- Wing Thumb

**APPLICATIONS:**

TSA, Construction, Forestry



**TECHNICAL DATA FOR: 34411**

<b>Series</b>	Luminator	<b>HI VIS</b>	High Visibility
<b>Material Group</b>	Leather		
<b>Product Type</b>	Drivers		
<b>Glove Size</b>	Large		
<b>Material</b>	Leather		
<b>Leather Cut</b>	Grain		
<b>Leather Type</b>	Pig Skin		
<b>Grade</b>	Premium		
<b>Features</b>	Waterproof		
<b>Insulated</b>	Insulated		
<b>Lining</b>	Thermosock		
<b>Pattern</b>	Gunn		
<b>Thumb Style</b>	Wing		
<b>Thickness</b>	0.6 - 1.4 mm		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved



**MCR**  
SAFETY

# 34411

## Luminator

### Drivers

### Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
34411L	Large	9.750	6.255	N/A	34.248 lb.	5.708
34411M	Medium	9.250	5.700	N/A	32.058 lb.	5.343
34411S	Small	8.81	5.380	N/A	29.040 lb.	4.840
34411XL	X - Large	9.850	6.255	N/A	35.460 lb.	5.910

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved