



**MCR
SAFETY**

N9674

Ninja

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. Common features to all styles include individual packaging for point of sale presentation, treated with Actifresh® to kill bacteria and promote freshness, and available in sizes small through extra large.

FEATURES:

- 15 guage black nylon/Lycra shell.
- Bi-Polymer Palm and Fingertips coated
- Great dexterity and sense of touch
- Comfortable and Cool
- EN388 score 412X

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling, Agriculture, Assembly Line Production, Automotive , Carpentry, Janitorial , Manufacturing, Warehousing



TECHNICAL DATA FOR: N9674

Series	Ninja	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	2
Glove Size	Large	EN 388 : CE Score - Puncture	X
Gauge	15 Gauge	ANSI Abrasion	ANSI Abrasion 4
Material	Nylon		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

N9674

Ninja

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9674L	Large	13.63	4.88	3.39	17.436 lb.	1.453
N9674M	Medium	13.00	4.56	3.35	18.024 lb.	1.502
N9674S	Small	12.60	4.24	3.35	14.772 lb.	1.231
N9674XL	X - Large	14.33	5.15	3.70	20.340 lb.	1.695

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved