

Flush Rectangular Non-Metallic Floor Boxes with Non-Metallic Covers

Style	1-Gang	2-Gang	3-Gang
	<p>PFBRG1*</p>	<p>PFBRG2</p>	<p>PFBRG3</p>
Min. Depth of Pour	3.00" (76.2)	3.00" (76.2)	3.00" (76.2)
Adjustability	Fully	Fully	Fully
Cubic Inch (cm ³) Capacity per Gang	14.3 cu. in. (234.3 cm ³) per 1" depth	14.3 cu. in. (234.3 cm ³) per 1" depth	14.3 cu. in. (234.3 cm ³) per 1" depth
Dimensions – A	6.00" (152.4)	6.00" (152.4)	6.00" (152.4)
Dimensions – B	3.60" (91.4)	6.80" (172.7)	10.04" (255.0)
Dimensions – C	5.47" (138.9)	5.47" (138.9)	5.47" (138.9)
Dimensions – D	6.90" (175.3)	6.90" (175.3)	6.90" (175.3)
Dimensions – E	5.41" (137.4)	8.56" (221.4)	11.75" (298.4)
Hubs	(4) 1¼"	(6) 1¼"	(8) 1¼"
Reducers	(4) 1" to ¾" and (4) 1¼" to 1"	(6) 1" to ¾" and (6) 1¼" to 1"	(8) 1" to ¾" and (8) 1¼" to 1"
Concrete Cover Included	✓	✓	✓
Closure Plugs Included	✓	✓	✓
Removable LV Barrier	–	✓	✓

Note: UL File Number E92074.

*Suitable for single service applications only.

Flush Rectangular Non-Metallic Covers and Flanges*

Required Components for Carpet Applications

Carpet Flanges				Cover with Duplex and Style Line® decorator inserts included		
Number of Gangs	1-Gang	2-Gang	3-Gang	One Required per Gang		
Dimensions	6.00" x 4.88"	6.00" x 8.13"	6.00" x 11.35"	4.15" x 2.97"		
Black	PFBRFBL1	PFBRFBL2	PFBRFBL3	PFBR826BLA		
Brown	PFBRFBR1	PFBRFBR2	PFBRFBR3	PFBR826BRA		
Gray	PFBRFGY1	PFBRFGY2	PFBRFGY3	PFBR826GYA		
Ivory	PFBRFI1	PFBRFI2	PFBRFI3	PFBR826IA		
				<p>Cover</p>	<p>Duplex Insert</p>	<p>Style Line® Decorator Insert</p>

Required Components for Tile Applications

Mounting Collar		Cover with Duplex and Style Line® decorator inserts included		
One Required per Gang	Cover Frame	One Required per Gang	One Required per Gang	
	Dim. 4.47" x 3.25"		4.15" x 2.97"	
PFBRMC	PFBRFRA	PFBR826GYA		
		<p>Cover</p>	<p>Duplex Insert</p>	<p>Style Line® Decorator Insert</p>

Note: *Flush rectangular non-metallic covers and flanges are UL listed only. Not CSA certified.

Dimensions in Inches (mm)