



## Main

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Side shield Pedal shield
Operator Action	Spring return with latch
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508
Height	4.84 in (123 mm)
Width	5.39 in (137 mm)
Depth	9.02 in (229 mm)

## Ordering and shipping details

Category	21441 - 9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	785901816614
Nbr. of units in pkg.	1
Package weight(Lbs)	4.69 lb(US) (2.127 kg)
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	13.97 in (35.484 cm)
Package 1 width	5.50 in (13.97 cm)
Package 1 Length	35.48 in (90.129 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	120
Package 2 Weight	576.00 lb(US) (261.269 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------