

# Dayton®

## Mod: 2H618C

- AC GEARMOTOR /
- Motor de Engranajes
- Reductores de CA /
- Moteur & Engrenage CA

HP/CV  V  A


RPM  TORQUE   
 TR/MIN PAR COUPLE

HZ  PHASE  RATIO  SERVICE FACTOR   
 FASE RELACION FACTOR DE SERV.  
 PHASE RAPPORT COEF. DE CHARGE

INSUL. CLASS  MAX. AMB.  CONT. DUTY  
 CLASE DE AISLAMIENTO AMB. MAX. SERVICIO CONTINUO  
 CLASSE ISOLATION AMB. MAXI. EN SERVICE CONTINU

TO REVERSE ROTATION INTERCHANGE RED AND BLUE LEADS.  
 PARA INVERTIR LA ROTACION INTERCAMBIE LOS ALAMBRES ROJO Y AZU.  
 POUR INVERSER LA ROTATION INTERCHANGER LES CONDUCTEURS ROUGE ET BLEU

Dayton Electric Mfg. Co.,Niles, Illinois 60714 U.S.A.



Made in U.S.A./Fab. en EE.UU./Fab. aux E.U.  
 Manf. for/Fab. para/Fab. pour

NAMEPLATE 129-650-1413