

ACTIVARMR®

PERSONAL PROTECTIVE GEAR

70-761

Outstanding Mechanical Protection

Previously known as: Vantage® 70-761



Cut



Medium Duty

Premium longevity and cut protection through advanced technology

- The optimal combination of cut resistance, comfort and dexterity. These premium gloves use innovative technology for improved cut resistance, excellent flexibility and a higher level of user comfort
- Versatility. The ActivArmr® range offers protection profiles for a wide variety of environments. Along with high cut resistance, most ActivArmr® gloves include protection from heat and light molten splashes



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Chassis assembly, body trimming
- Welding
- Seizing rough blocs and cylinders
- Seizing and finishing structural parts
- Seizing structural parts
- Foundry operations
- Handling materials with sharp or rough edges
- Handling parts in high heat areas

ACTIVARMR®

PERSONAL PROTECTIVE GEAR

70-761

Outstanding Mechanical Protection

Previously known as: Vantage® 70-761

Key Features

- Reinforced thumb crotch with 100% Kevlar®
- High level of cut protection
- Excellent abrasion resistance due to exclusive fibre blend
- Design to fit the natural contours of the hand

Technologies

Kevlar®

Performance Standards & Regulatory Compliance

REACH Compliant



1X4XD



244X



X1XXXX



0493



ABR



CUT

Specifications

| BRAND STYLE | DESCRIPTION | Gauge | SIZE | LENGTH | PACKAGE |
|------------------|--|-------|--------------------|--------------------------------|---|
| ActivArm® 70-761 | Liner Material: DuPont™ Kevlar®, Nylon, Acrylic Cuff Style: Knitwrist | 10 | 6, 7, 8, 9, 10, 11 | 225-275 mm / 8.85-10.82 inches | • 12 pairs in a bag; 6 bags in a carton |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.