

ACTIVARMR®

PERSONAL PROTECTIVE GEAR

70-765

Outstanding Mechanical Protection

Previously known as: Vantage®70-765



Cut

Abrasion Protection



Heat



Heavy Duty

Advanced cut protection combined with premium leather for superior grip

- Now with reinforced thumb and seams relocated to the backs of the fingers, reducing exposure to cuts and offering greater protection and longer life. This new design helps guard against minor injuries and punctures, as well as offering superior grip even in oily environments thanks to use of premium leather in the palm
- Plaited inside for comfort with coloured polyester/cotton
- Palm reinforced with premium leather



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Handling rough machined metal parts
- Glass repair and replacement
- Seizing rough blocs and cylinders
- Handling materials with sharp or rough edges
- Press shop operations

ACTIVARMR®

PERSONAL PROTECTIVE GEAR

70-765

Outstanding Mechanical Protection

Previously known as: Vantage®70-765

Key Features

- Durable leather pad double-stitched with DuPont™ Kevlar® fiber to ensure superior grip and protection against sharp snags and punctures
- Engineered yarns provide high cut protection-to-weight ratio
- 10-gauge, mediumweight cut resistant yarn and reinforced thumb crotch
- Protection all the way to the fingertips
- Protects hands from intermittent heat contact up to 100°C / 200°F
- Also available in vend pack

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies

Kevlar®

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
ActivArm® 70-765	Finishing: Leather Palm Coating Material: Leather Liner Material: Acrylic, Nylon, Kevlar® Cuff Style: Knitwrist	10	8, 9, 10, 11	235-275 mm/ 9.25-10.82 inches	Grey	• 12 pairs in a bag; 3 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.