

Decorator Weather Resistant, Tamper-Resistant, Standard and Single Receptacles

Decorator Duplex Receptacles, 2 Pole, 3 Wire

Description	Weather and Tamper-Resistant	Tamper-Resistant	Standard	Standard
	Termination	Self-Grounding, Push and Side Wire	Self-Grounding, Push and Side Wire	Self-Grounding, Push and Side Wire
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R
Black	RRD15SBKWRTR	RRD15SBKTR	RRD15SBK	RRD15BK
Brown	RRD15SWRTR	RRD15STR	RRD15S	RRD15
Gray	RRD15SGYWRTR	RRD15SGYTR	RRD15SGY	RRD15GY
Ivory	RRD15SIWRTR	RRD15SITR	RRD15SI	RRD15I
Light Almond	RRD15SLAWRTR	RRD15SLATR	RRD15SLA	RRD15LA
White	RRD15SWRTR	RRD15SWTR	RRD15SW	RRD15W



RRD15SWTR

Description	Tamper-Resistant, Nightlight Receptacle	Tamper-Resistant	Tamper-Resistant, Without Ears**
	Termination	Self-Grounding, Two Nightlight Sources for 0.5 Lumens Total, Back and Side Wired	Self-Grounding, Eight Push Wire Holes Only #14 AWG
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R
Black	—	RRD15EBKTR	RRD15KBKTR
Brown	—	RRD15ETR	RRD15KTR
Gray	—	RRD15EGYTR	RRD15KGYTR
Ivory	DR15NLIV	RRD15EITR	RRD15KITR
Light Almond	DR15NLLA	RRD15ELATR	RRD15KLATR
White	DR15NLWH	RRD15EWTR	RRD15KWTR



RRD15SW



DR15NLWH

Note: See page Tech-10 for Weather and Tamper-Resistant descriptions.
**100 per case, bulk packed. Mounting screws inserted into strap.

Decorator Single Receptacles, 2 Pole, 3 Wire

Description	Tamper-Resistant	Tamper-Resistant	Standard
	Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Rating	15A 125V NEMA 5-15R	20A 125V NEMA 5-20R	20A 125V NEMA 5-20R
Black	RRD151BKTR	RRD201BKTR	RRD201BK
Brown	RRD151TR	RRD201TR	RRD201
Gray	RRD151GYTR	RRD201GYTR	RRD201GY
Ivory	RRD151ITR	RRD201ITR	RRD201I
Light Almond	RRD151LATR	RRD201LATR	RRD201LA
White	RRD151WTR	RRD201WTR	RRD201W



RRD151W

Description	Standard	Standard
	Termination	Self-Grounding, Side Wire
Rating	15A 250V NEMA 6-15R	20A 250V NEMA 6-20R
Black	RRD155BK	RRD205BK
Brown	RRD155	RRD205
Gray	RRD155GY	RRD205GY
Ivory	RRD155I	RRD205I
Light Almond	RRD155LA	RRD205LA
White	RRD155W	RRD205W



RRD205W

Note: See page Tech-10 for Tamper-Resistant description.

Dimensions in Inches (mm)