

# B18 Combination Box/Conduit Hanger – 812MB18A



- One assembly provides support for horizontal electrical box and/or conduit from threaded rod
- Eliminates need for offset bending conduit
- 66% less Drop Wires (rod/wire application)
- NEC® & CEC compliant



|                             |                    |
|-----------------------------|--------------------|
| Part Number                 | 812MB18A           |
| Material                    | Spring Steel       |
| Finish                      | nVent CADDY Armour |
| EMT Conduit Size            | 1/2"<br>3/4"       |
| Hole Size (HS)              | 1/4"               |
| Hole Type                   | Plain              |
| Screw Included              | No                 |
| Certifications              | cULus              |
| Standard Packaging Quantity | 25 pc              |
| UPC                         | 78285652002        |

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.

NEC is a registered trademark of, and National Electrical Code (NEC) standard is a copyright of the National Fire Protection Association, Inc. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

