

Threaded Bridle Ring – 4BRT32WS



- Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.



Part Number	4BRT32WS
Material	Steel
Finish	Electrogalvanized
Diameter	2"
Screw Diameter	#14
Screw Type	Wood
Screw Length	3/4"
Ultimate Static Load	50 lb
Certifications	cULus ITB
Standard Packaging Quantity	100 pc
UPC	78285676928
EAN-13	8711893061260

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2021 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

