

Convenient Ground Electrode Kit – CGE5CP



- Kit includes two ground rods, ground clamp, compression coupler and drive sleeve
- UL®-Listed and NEC®-Compliant
- Allows for installation from ground level
- Two 4' (1.2 m) ground rods with coupler provide more convenient storage and transportation than one 8' (2.4 m) ground rod



Part Number	CGE5CP
Material	Copper-Bonded Steel Bronze
nVent ERICO Ground Rods	615840
Clamp	CP58
nVent ERICO Drive Sleeve	EDS58
Conductor Size	#8 Solid - #2 Stranded 10 mm ² Solid - 35 mm ² Stranded
Certifications	UL
Standard Packaging Quantity	1 pc
UPC	78285659464
EAN-13	8711893044003

Included in this Kit

Part Number	Description	Quantity
615840	Copper-Bonded Ground Rod, Pointed, 5/8" dia, 4', 10 mil Plating, 3.4 lb	2
CP58	Ground Rod Clamp, Rod to Conductor, Bronze, Silicon Bronze, 1/2"-5/8" dia, #10 Solid-#2 Stranded, 6 mm ² Solid-25 mm ² Stranded, 1/2" Wrench	1
EDS58	Ground Rod Drive Sleeve for Pointed Ground Rods, 5/8" dia, 2.5"	1

NEC is a registered trademark of, and National Electrical Code (NEC) standard is a copyright of the National Fire Protection Association, Inc. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.