



Core & Coil (71A) MH ~LT~ 175W

CORE & COIL HID MH BAL 50W M110 120/277V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	M110
Lamp Type	50W MH
Number of Lamps	1 piece/unit
Circuit Type	HX-HPF
Ballast Type	Magnetic HID
Base Model	71A5181
Core Size	3 X 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI533-H4
Ignitor Temperature Rating	105°C
Capacitor Value	6 MFD
Capacitor Catalog Number	7C060L30RA
Capacitor Requirements	280V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.25 in
Capacitor Height	2.75 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	120/277 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	1.2/0.51 A
Input Current (Starting)	0.46/0.2 A
Input Current (Short Circuit)	0.42-0.65/0.16-0.27 A
Secondary Short Circuit Current	0.7-0.88 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	254 V
Input Current (Operating) (Nom)	0.58/0.25 A A
Input Power (Nom)	67 W
Rated Lamp Watts	50 W


Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes

Core & Coil (71A) MH ~LT~ 175W

Max Ballast-Lamp Distance Remote Wiring	10'
Recommended Fuse Value	3/2 A
Approval and Application	
Open Circuit Voltage Test (Volts)	228-280 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A/A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

Product Data	
Order product name	CORE & COIL HID MH BAL 50W M110 120/277V KIT
EAN/UPC - Product	781087056028
Order code	71A5181001D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710635601
Net Weight (Piece)	2.201 kg

Dimensional drawing



MH BAL 50W M110 120/277V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 50W M110 120/277V KIT	2.23 in	1.18 in	3.9 in	3.5 in	2.8 in	2.4 in

