

Waber-by-Tripp Lite 6-Outlet (77.6mm center-to-center spacing) Industrial Power Strip, 6-ft. Cord

MODEL NUMBER: **6SPDX**



Highlights

- 6 outlets
- 6-ft. cord
- 12.5-in. length
- Lighted master switch
- All-metal housing

Package Includes

- 6SPDX Power Strip
- Warranty information
- Instruction manual

Description

The Waber-by-Tripp Lite 6SPDX Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing, 6-foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 6SPDX ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R
 ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)
 FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-foot AC line cord

Specifications

OVERVIEW	
UPC Code	037332108234



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Spacing	1.520 in.
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted combination switch / circuit breaker
PHYSICAL	
Anti-Microbial Protected	No
Color	Beige
Color (AC Line Cord)	Beige
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	203.20mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	77.60mm
Receptacle Color	Beige
Shipping Dimensions (hwd / cm)	5.72 x 15.24 x 36.20
Shipping Dimensions (hwd / in.)	2.25 x 6.00 x 14.25
Shipping Weight (kg)	1.04
Shipping Weight (lbs.)	2.30



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
Canada	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>