

Tools for Building, Construction, Engineering and Design Professionals



Model 4020

Easy-to-use, the Measure Master Pro meets the challenge for fast, accurate solutions in the office or on the jobsite. Carry it in your tool box or briefcase.

Built-in Functions Provide Problem Solving Benefits

- Quickly find solutions to building and dimensional problems
- Enter the numbers just as you would say them
- Reduce expensive errors when estimating dimensions, costs and materials



4840 Hytech Drive
Carson City, NV 89706
1-775-885-4900
Fax: 1-775-885-4949
Visit our website at:
www.calculated.com

MEASURE MASTER PRO™

MODEL 4020

Feet-Inch-Fraction and Metric Calculator

Get professional results every time with this handy and easy-to-use tool for projects involving measurements! Work in and convert between dimensional formats including Feet-Inch-Fractions; Decimal-Feet-Inch-Fractions, Yards, Meters, Centimeters and Millimeters, as well as Areas and Volumes. The **Measure Master Pro** is ideal for faster, more accurate material estimates. Quickly solve Circumference, Circle Area and Arcs. Use it at home or in the shop for on-the-spot calculations for all your projects — saving you time and money!




Work In and Convert Between Dimensions, including Metric



Linear, Area and Volume Measurements



Find Weight and Weight per Volume



Instant Solutions for Circle Area, Circumference, Arcs and More

Measure Master Pro is the choice for:



- Designers
- Craftsmen



- Tradespersons
- Fabricators



- Woodworkers
- Technicians

Product Specifications — Measure Master Pro Model 4020

Size:	5.6" x 3.0" x 0.6" (142.8mm x 76.2mm x 15.9mm)
Weight:	4.5 oz. (127.5 gm) Includes Case and Field Reference Guide
Power:	Two 3-volt (LR-44/A76) Long-life Batteries
Display:	11 Digits (7 normal, 4 fractions) with Full Annunciators
LCD Dimensions:	0.625" x 2.5" (15.88mm x 63.5mm)
Accuracy:	10 Digit Internal Accuracy

Included with Every Measure Master Pro:

Protective Hard Slide Cover; Long-life Batteries (Two LR-44); English and Spanish Quick Reference Guides and Pocket Reference Guides.

Full One-Year Limited Warranty:

All Calculated Industries calculators and electronic tools are covered by a Full One-Year Limited Warranty against defects in materials and workmanship. The full text of each warranty is published in the documentation accompanying each product and at www.calculated.com. Calculated Industries reserves the right to make changes in the materials and specifications of products without notice.



Fast, Accurate Solutions for Building Professionals

Compare Calculator Features:

	CONSTRUCTION MASTER PRO 4065	CONSTRUCTION MASTER PRO IRG 4080	CONSTRUCTION MASTER PRO DT 44065	CONSTRUCTION MASTER PRO DESKTOP 44080	MEASURE MASTER PRO 4020
Dimensional Math and Conversions					
Feet-Inch-Fraction, Inch Fraction, Yards	✓	✓	✓	✓	✓
Decimal Feet (10ths, 100ths), Decimal Inches	✓	✓	✓	✓	✓
Preset Fractions (1/2" through 1/64")	✓	✓	✓	✓	✓
D:M:S, Decimal Degree Entry and Conversions	✓	✓	✓	✓	✓
Full Metrics (m, cm, mm)	✓	✓	✓	✓	✓
Right Angle Solutions					
Complete Right Angle/Rafter Calculations	✓	✓	✓	✓	
Pitch Key (Slope and Grade)	●	●	✓	●	
Rise, Run, Diagonal/Common Rafters	✓	✓	✓	✓	
Hip/Valley Key	✓	✓	✓	✓	
Jack Rafters Key	✓	✓	✓	✓	
Irregular Hip/Valley and Jacks	✓	✓	✓	✓	
Rafter Cutting angles (Plumb, Cheek and Level Cuts)	✓	✓	✓	✓	
Stair Layout Key	✓	✓	✓	✓	
Stair (Advanced – Riser Limit, Stairwell Opening, Headroom, Floor Thickness)	●	●		●	
Diagonal Key	✓	✓	✓	✓	
Expanded Rake-Wall	✓	✓	✓	✓	
Arched Rake-Wall	●	●		●	●
Studs: Find number On-center	●	●		●	
Area and Volume Solutions					
Square and Cubic	✓	✓	✓	✓	✓
Roof – Bundles, Squares, 4x8 Sheets, Pitch, Plan Area	●	●		●	
Drywall, Siding and Paneling 4x8, 4x9 and 4x12	●			●	
Column/Cone Area and Volume	✓	✓	✓	✓	
Basic Circular Calculations	✓	✓	✓	✓	✓
Advanced Circular Calculations	✓	✓	✓	✓	✓
Weight per Volume Conversions	✓	✓	✓	✓	✓
Length, Width and Height Keys	●			●	●
Block, Footings	✓		✓	✓	
Special Functions					
Trigonometric Function Keys (Sine, Cosine, Tangent, Arcsine, Arccosine, Arctangent)		✓	✓	✓	
Board Feet	✓	✓	✓	✓	✓
Works as a Regular Calculator (+, -, ×, ÷, +/-, %, π, 1/x, x ² , √x)	✓	✓	✓	✓	✓
User-Definable Preferences	✓	✓	✓	✓	✓
Entry Editing Backspace Key	✓	✓	✓	✓	✓
Cost per Unit (Total costs based on unit price)	✓	✓	✓	✓	✓
Equal sided Polygon	●	●		●	
Compound Miters	●	●		●	
Crown Angle	●	●		●	
Additional Capabilities and Characteristics					
Paperless Tape	✓	✓	✓	✓	✓
Number of Memories	● 4	● 4	3	4	4

● = New or Enhanced Features/Functions

MEASURE MASTER PRO™

MODEL 4020

Feet-Inch-Fraction and Metric Calculator

DESIGNERS • TRADESPERSONS • WOODWORKERS • CRAFTSMEN
FABRICATORS • TECHNICIANS

Dedicated Keys and Functions Make It Easy To Use

Length, Width, Height — Area, Volume, Square-up, Perimeter, Wall Area, Room Area

m, cm, mm — Work in Metric Dimensions

Yds, Feet, Inch, / — Work in Yards, Feet, Inches, Fractions

Conv — Convert to all secondary functions and features

Stor/Prefs — Store and set preferences for Fractions, On-center, Area, Volume, Metric, Degrees

Circ — Advanced Circular Calculations including Area, Circumference, Diameter

Arc — Arc°, Chord, Segment and Pi, Area, Rise, On-center

BdFt — Find total Board Feet

Backspace Key — Easily change entries

= — Paperless Tape

Measure Master Pro™ is a trademark and Calculated Industries® is a registered trademark of Calculated Industries, Inc. © 2006. All rights reserved.

4020v3.1-SPEC-4C-08_06