



Nitrile

Consistent comfort and durability

- Fully textured for enhanced grip
- Consistent, dependable protection
- Enhanced tactile sensitivity
- Tested for use with chemotherapy/cytotoxic drugs



Industries

- Food Processing
- Life Sciences
- Healthcare

Recommended For

- Equipment, maintenance and repair
- All food processing, applications that have food contact
- Sample taking and processing
- Standard, moderate risk examination procedures
- Protection from Type I latex allergy in HCW's or patients



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	Cobalt® N19
Material	Nitrile
Color	Cobalt
Glove Design	Chlorinated, Powder-Free, Fully Textured
Cuff	Beaded
Manufacturing/QMS Audit Standards	EN ISO 13485 : 2012
Regulatory/Standards Compliance	ASTM D6319, EN 420:2003 + A1:2009, FDA21 CFR 177-2600, US QSR/FDA 510(k) Medical Examination Grade
Packaging	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition
Country of Origin	China
User Needs Segment	Multi-Purpose
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D3767,EN420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.10 / 3.9		ASTM D3767,EN420
Finger Thickness (mm/mils)	0.11 / 4.3		ASTM D3767,EN420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 21	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
63000 Cyberjaya
Selangor, Malaysia
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ahcenn PYC
123610 Poccnr, Mockba
Kpachonpechehckar
Ha6. 12, n.3, op. 1304A
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.