



Nitrile

## Black nitrile exam gloves that offer reliable protection for messy jobs

- Deep black color masks stains and makes viewing lighter objects easy
- Textured fingers for consistent grip
- Suitable for use in a wide range of industries and applications



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Healthcare

### Recommended For

- Inspection, selecting, checking parts
- Equipment repair and maintenance
- Inspection (picking, checking and marking)
- Inspection
- Body surface checking, marking and touching up
- Painting or cleaning tools or robots
- Standard, moderate risk examination procedures
- Protection from Type I latex allergy in HCW's or patients



## TECHNICAL DATA SHEET

### PRODUCT INFORMATION

	<b>Onyx<sup>®</sup> N64</b>
<b>Material</b>	Nitrile
<b>Color</b>	Black
<b>Glove Design</b>	Chlorinated, Powder-Free, Silicone Free, Textured Fingers
<b>Cuff</b>	Beaded
<b>Manufacturing/QMS Audit Standards</b>	ISO 13485:2003
<b>Regulatory/Standards Compliance</b>	ASTM D6319, EN 420:2003 + A1:2009, FDA21 CFR 177-2600, US QSR/FDA 510(k) Medical Examination Grade
<b>Packaging</b>	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
<b>Storage</b>	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
<b>Country of Origin</b>	Malaysia
<b>User Needs Segment</b>	Multi-Purpose
<b>Available sizes</b>	S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11)
<b>Anti-static</b>	Not Tested

### PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.09 / 3.5		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.13 / 5.1		ASTM D3767,EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	≥ 33	≥ 29	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412

### ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
<b>Product Code</b>	N641	N642	N643	N644	N645

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ansell PYC  
Ten. +7 495 258 13 16

Performance Standards and  
Regulatory Compliance



Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.