

NEW!

3754 ELECTRONIC HEIGHT GAGE

Starrett®

METROLOGY SOLUTIONS

At Starrett, we know what you look for in precision measurement:

- Accuracy
- Fast Adjustment
- Quick Lock

This electronic height gage has it.



NEW!

3754 ELECTRONIC HEIGHT GAGE

METROLOGY SOLUTIONS



3754-12/300

FEATURES

- Large (.380"/9.65mm), easy-to-read LCD display reads to .0005" or 0.01mm.
- Large positive action keypad.
- Relative scale.
- Fine adjust.
- Furnished with two (2) 3-volt batteries (CR2032) and carbide tip scriber.
- Improved battery cover.

Functions

in/mm Hold ± Zero Set Preset Limit Output Auto Off

3754 Electronic Height Gage

Cat. No.	EDP	Range	Accuracy	Resolution
3754-12/300	72625	0-12" (300mm)	0.001"	.0005"
3754-24/600	46003	0-24" (600mm)	.002" (>18")	.0005"

ACCESSORIES



Cat. No.	EDP
3908AC	12636

Includes contact points, dovetail clamp and two post holder.



Cat. No.	EDP
PT99454	68713



Cat. No.	EDP
PT22357	12295



Cat. No.	EDP
3259-AC	69859



Cat. No.	EDP
733SCKB	69888



Cat. No.	EDP
733SCU	69898



Cat. No.	EDP
1500-1-N	12745



Cat. No.	EDP
1500-3A-3N	12532



Cat. No.	EDP
719	66490



Cables, Accessories, Cases for 3754 Electronic Height Gages

Cat. No.	EDP	Description
PT61120	65446	3-volt battery, CR2032 (2), required
928	55249	Wood case only for 12" gage
945	56684	Wood case only for 24" gage
733SCKB	69888	USB cable to PC running Excel
733SCU	69898	USB cable to PC running SPC Data Collection software
733SCM	69893	Cable to 7612 or 7613 Multiplexer

Furnished without case unless otherwise ordered.

STARRETT HEIGHT GAGE FAMILY

Advanced ←

→ Economy



Altissimo



DigiCheck



252



3754



254



3751



3250