



TAMETO LED FACILITY LIGHTING

QUALITY AND VERSATILITY FOR ERGONOMIC WORKSTATION LIGHTING



TAMETO offers broad, bright light output for workbenches and assembly workstations in an efficient, ergonomic design. It reduces glare, eye strain and fatigue, providing a comfortable work environment for long workdays. Strong, sleek and minimalistic, TAMETO is ideal for applications ranging from assembly and production to quality control inspections.

FEATURES:

- Various lengths for different bench widths and lighting requirements
- Up to 60% energy savings and up to 40% higher illuminance compared to conventional CFL lamps
- Latest LED technology with a service life of up to 50,000 hours
- Fixed or suspended installation options available
- Minimal heat generation
- Integrated T-slots allow direct installation into truss type workstations
- Extremely strong aluminum housing

SPECIFICATIONS:

Voltage	120-277V
Light Source	LED
Lumens Range	1400 - 3200
Controls	rocker switch
Color Temperature	4000K or 5000K
Color Rendering Index (CRI)	80
Luminaire Head Material	anodized aluminum
Lens Material	PMMA acrylic
Luminaire Dimension	varied lengths, 7.4" width
Power Consumption	various
Protection Rating	IP20
Cord/Plug	9' cord with plug
Certification	CE, ETL/cETL
Mounting	Brackets included

Various mounting options and accessories available






Mounting bracket included

DIMENSIONAL DATA



TAMETO Linear Fixed Mount





Measurements in millimeters

ORDERING INFORMATION							
Wattage	Light Source	Length (A)	Mounting	Lumens	Model	Part #	
33W	LED	49.5" (1256mm)	Linear fixed	3200	SAHQ 88	112 979 000 - 005 556 77	
26W	LED	37.6" (956mm)	Linear fixed	2400	SAHQ 66	112 975 000 - 005 556 19	
18W	LED	25.8" (656mm)	Linear fixed	1500	SAHQ 44	112 971 000 - 006 361 65	
18W	LED	17.9" (456mm)	Side mount	1400	SAHKQ 60	112 989 000 - 006 364 07	
33W	LED	49.5" (1256mm)	Linear fixed	3200	SAHQ 88	112 980 000 - 005 513 364	

Thru-wire options available. Call for details.

Mounting Options	Item	Unit	Part #
	Swivel mounting brackets for linear fixed model	Sold as pair	408 001 586 - 005 780 88

Waldmann Lighting Company

9 Century Drive Wheeling, Illinois 60090 www.waldmannlighting.com Telephone (847) 520 1060 Fax (847) 520 1730 waldmann@waldmannlighting.com

