



9430 RALS



- Built Pelican tough
- New improved version - Generation 3
- Up to 15 hours of run time
- 3000 lumens of brightness
- Maintenance Free LED Array with life expectancy of 50,000 hours
- Fully extendable mast with 360 degree rotating head
- Low Battery Warning System
- Waterproof Rubber Activation Switch
- Mast Extension Lock
- RoHS and CE Compliant

DIMENSIONS

Head (L x W x D): 6.50 x 7.87" x 2.56 (16.5 x 20 x 6.5 cm)

Closed (L x W x D): 15.75 x 7.87" x 9.06 (40 x 20 x 23 cm)

Light Head Height (max): 32.28" (82 cm)

Cord Length: 13.78" (35 cm)

MATERIALS

Body: Polycarbonate (PC) / ABS

Head: Polycarbonate (PC) / ABS

Mast: Glass-Reinforced Plastic

Lens: Polycarbonate (PC)

COLORS

■ Black

■ Yellow

LIGHT SPECS

Lumens (High): 3000

Lumens (Low): 1500

Lamp Heads: 1

Lamp Type: LED

Number of LEDs: 6

Lamp Life: 50000 hrs

Beam Spread: 125°

IP Rating: 54

POWER

Run Time (High): 8.00 hrs

Run Time (Low): 15.00 hrs

Battery Type: Sealed Lead Acid (SLA)

Battery Lifespan: 500 cycles

Charge Time: 5 hrs

Battery Level Indicator: Intermittent Blinking

Sockets (Primary): 1

Sockets (Aux): 1

Volts: 12.0v

WEIGHT

Weight: 22.65 lbs (10.3 kg)

SWITCH

Switch Type: Silicone Rubber Keypad

Pelican Products, Inc.

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311

sales@pelican.com • www.pelican.com