





M-12034 3

GREEN DOT ON
HOSPITAL GRADE ONLY
RED DOT ON
SNAP5362WAM1 ONLY



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BODY	NYLON	SEE TABLE
BASE	NYLON	
LINE CONTACTS	BRASS	
GROUND CONTACT	BRASS	
BRIDGE	SEE NOTES	SEE NOTES
DRIVE SCREWS	ST. STEEL	
RIVETS	BRASS	
MOUNTING SCREWS	STEEL	ZINC PLATE
GROUNDING CLIP	ST. STEEL	
WASHER	FIBER	

CATALOG NO. SNAP8300A
(NOT SHOWN TO SCALE)



SYM	REVISIONS	APP	DATE
3	ADDED CATALOG No. SNAP5362WAM1 TO TABLE; ADDED RED DOT FOR SNAP5362WAM1 ONLY TO GREEN DOT CALLOUT PER DCN 23610 RM	DJP	2/26/18
2	REDRAWN WITH EMBEDDED CAD MODEL WITH NO CHANGES TO PART GEOMETRY. PER DCN 21895 SPN	DJP	02/05/16
1	RELEASE FOR PRODUCTION PER DCN 18212	C.Z	09/15/2011

CATALOG NO		COLOR	CONFIGURATION	RATING
STANDARD	HOSPITAL			
SNAP5262A	SNAP8200A	BROWN	NEMA 5-15R	15A 125V
SNAP5262IA	SNAP8200IA	IVORY		
SNAP5262GYA	SNAP8200GYA	GREY		
SNAP5262RA	SNAP8200RA	RED		
SNAP5262WA	SNAP8200WA	WHITE		
SNAP5262BKA	SNAP8200BKA	BLACK		
SNAP5262ALA	SNAP8200ALA	ALMOND		
SNAP5262LAA	SNAP8200LAA	LIGHT ALMOND		
SNAP5362A	SNAP8300A	BROWN	NEMA 5-20R	20A 125V
SNAP5362IA	SNAP8300IA	IVORY		
SNAP5362GYA	SNAP8300GYA	GREY		
SNAP5362RA	SNAP8300RA	RED		
SNAP5362WA	SNAP8300WA	WHITE		
SNAP5362BKA	SNAP8300BKA	BLACK		
SNAP5362ALA	SNAP8300ALA	ALMOND		
SNAP5362LAA	SNAP8300LAA	LIGHT ALMOND		

NOTES: UNLESS OTHERWISE SPECIFIED

1. ALL CATALOG NOS ARE FED SPEC, UL AND CSA CERTIFIED

2. HOSPITAL GRADE SUPPLIED WITH BRASS BRIDGE AND DRIVE SCREWS, STANDARD GRADE SUPPLIED WITH ZINC PLATED STEEL BRIDGE WITHOUT DRIVE SCREWS

3. ALL DIMENSIONS ARE IN INCHES [mm].

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
SNAPCONNECT, HUBBELL
DUPLEX RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY F.H	APP. BY C.Z
	TR. BY	SCALE 1:1
	CHK. BY C.Z	DATE 6/20/2011

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE

NON-REPAIRABLE

B

M-12034

3