Ø3.0" Tube Brush w/ 3' Flex Handle *likan* Series 53835 **Flexible Handle** Stainless steel holds bristles tight and allows for cleaning in tight spaces A STAIL REP

Soft Bristles

Ideal for sweeping fine particles and for wet use with cleaning agents

This tube and valve brush is designed to clean hard-to-reach areas. The soft bristles are attached to a helically wound stainless steel shaft, making it strong, FDA-compliant, and chemically resistant.



Ø3.0" Tube Brush w/ 3' Flex Handle 53835

Available in white only

The 3' flex handle lets the tube brush fits in curved pipes easily so the soft bristles can sweep out small particles. The brush can also be used with water and a cleaning agent for a washing effect.

Specifications:

Length: 36.25" Width: 3" Height: 3" FDA-Compliant Raw Material: Yes Material: Polyester/SS/Polypropylene Unit Weight: 0.37 lbs. Bristle Type: Soft

Colors

When ordering, add the color digit to the base part number to denote color.



Fully updated product specifications are available at Vikan.com.

The Color-Coding System

Remco and Vikan[®] brands offer an integrated color-coding system to help mitigate the risk of cross-contamination in food processing facilities. With an array of color-coded tools and



storage brackets, and years of experience building effective color-coding systems, the experts at Remco Products Corporation can help you effectively apply color-coding to divide and identify different zones or processing tasks. As a result, workers can more easily comply with material handling and hygienic cleaning procedures to maintain stringent food safety standards.



Please see the full-line catalog for a complete list of Remco[™] and Vikan[®] products.













Tubs



ikan

Remco Products Corporation

4735 West 106th Street Zionsville, Indiana 46077

PHONE: 317.876.9856 | FAX: 800.585.8619

www.remcoproducts.com

© 2017 Remco Products 3/17 RMC-P459 | Vikan® is a registered trademark of Vikan A/S. | Remco is the exclusive Vikan Partner in the United States.