

FAN-FORCED ELECTRIC WALL HEATERS



4300-Series



- Finned tubular steel element
- 20-gauge steel grill
- Manual reset thermal limit
- Propeller style fan blade
- Housing can be positioned vertically or horizontally

3200-Series



- Finned tubular steel element
- 18-gauge steel grill
- Manual reset thermal limit
- Propeller style fan blade
- Back can includes drywall depth embossments

3310-Series



- Block-finned steel element
- 18-gauge steel grill
- Automatic reset thermal limit
- Vane axial style fan blade
- Quiet, but provides a high CFM output of down flow air

FEATURES

- ETL C/US listed for indoor residential, commercial, & industrial heating applications
- Heavy-duty steel grill, with a WHITE powder-coated finish
- Single or double pole thermostats with 50° to 90° temperature range



BENEFITS

- Units can be recessed, or installed with an optional surface mounting frame
- Quiet operation with high performance hot air discharge
- Units have a standard thermal overload cutoff for added safety

APPLICATION SOLUTIONS

- Units are ideal for small hard to heat areas; such as bathrooms, vestibule areas, hallways, offices, hotels, stairways, etc.
- Designed for spot, supplement, and even primary comfort heating systems.

Indoor Spot Heating



120, 240/208 Volt Application



PRODUCT SERIES	Grill Dim (in.)			Rough-In Dim (in.)		
	H	W	D	H	W	D
4300-Series	7 5/8	16 3/4	1	7 1/8	14 1/2	3 1/2
3000-Series	13	9 25/32	1	9 1/4	12 1/8	3 5/8
3310-Series	20 3/64	15 3/8	1	14 3/16	19 15/16	4

SIZING CHART - WALL HEATER SERIES		
Product Series	Room Size	Coverage (sq. ft.)
4300-Series	Small	50-125
3200-Series	Small to Medium	50-175
3310-Series	Medium to Large	75-275

GRAINGER MODEL #	MFG MODEL #	WATTS	BTUs	VOLTS	AMPS	RPM	CFM	STAT TYPE	PRODUCT SERIES	GRILL COLOR	WT. (lbs.)		
31TR36	E4315TRPW	1500	5,120	120	12.5	2200	70	Single	4300-Series	White	9		
31TR37	HF4320T2RPW	2000/1500	6,826 / 5,120	240/208	8.3/7.2	2200	70	Double					
31TR39	E3215TRPW	1500	5,120	120	12.5	2200	70	Single					
31TR40	HF3215T2RPW	1500/1125	5,120 / 3,840	240/208	6.3/5.4	2200	70	Double	3200-Series		White	6	
31TR41	HF3222T2RPW	2250/1688	7,680 / 5,762	240/208	9.4/8.1	2200	70	Double					
31TR47	E3313TRPW	1500/750	5,120 / 2,560	120	12.5/8.3	600	175	Single	3310-Series			White	22
31TR48	HF3315T2RPW	3000/1125	10,240 / 3,840	240/208	12.5/5.4	600	175	Double					
31TR49	HF3316T2RPW	4000/1500	13,648 / 5,120	240/208	16.8/7.2	600	175	Double					

