




NOBLES[®]
ENGINEERED BY TENNANT COMPANY

SPEEDGLEAM[®] 5 & 7

Battery Powered Walk-Behind Burnishers

- 
- Ultra quiet machines - as low as 63 dBA - ensures safe sound levels
 - Passive dust control as standard - maintains indoor air quality
 - 90 degree flip up head - enables a safe ergonomic position when changing pad



High gloss results in an ultra quiet, ergonomic design



Tennant Company SpeedGleam® 5 & 7 Burnishers are the smart, reliable choice for your no-nonsense cleaning needs.

Nobles
 701 North Lilac Drive
 Minneapolis, MN 55422
 USA/Canada: +1.800.553.8033
 Quebec: +1.800.361.9050
 www.nobles.com
 nobles@tennantco.com

SpeedGleam® Burnishers	SpeedGleam 5		SpeedGleam 7	
	Pad Assist	Propel	Propel	Propel
Path width	20 in / 510 mm		24 in / 610 mm	27 in / 690 mm
Pad motor	36 V, 75 A, 2.8 hp max / 2.1 kW		36 V, 90 A, 3.6 hp max / 2.6 kW	
Pad speed	2,100 rpm		1,875 rpm	
Burnishing speed				
Min	Pad Assist	100 fpm / 30 mpm	100 fpm / 30 mpm	
Max	Pad Assist	200 fpm / 60 mpm	200 fpm / 60 mpm	
Transport speed (max)	—	240 fpm / 73 mpm	240 fpm / 73 mpm	
Battery				
Wet	3 - 12V, 185 Ah	3 - 12V, 225 Ah	6 - 6V, 240 Ah	6 - 6V, 330 Ah
AGM (opt)	3 - 12V, 234 Ah		6 - 6V, 312 Ah	
Wet (opt)	3 - 12V, 225 Ah	—	6 - 6V, 360 Ah	
Passive filtration	95% @ 0.3 microns		95% @ 0.3 microns	
HEPA filtration (opt)	99.97% @ 0.3 microns		99.97% @ 0.3 microns	
Sound level				
Passive	65 dBA		65 dBA	
Active	64 dBA		63 dBA	
ETL listed*	Yes		Yes	

1.619.001.am.en SpeedGleam 5 & 7 Burnishers 2/14
 ©2014 The Tennant Company logo and other trademarks designated with the symbol "®" are trademarks of Tennant Company registered in the United States and/or other countries. Tennant Company's products are sold and serviced through subsidiaries of Tennant Company and distributors. All rights reserved.



*U.S./Canada only
 Specifications subject to change without notice