

# 3330 TeleTalker™ 330 Linemen's Test Set

*Test Analog / POTS line and system for noise and intermittent connections*

## **Features:**

- Pulse and Tone dialing
- Three modes: data safe Monitor, Ring and Talk
- Selectable Pulse or Tone dialing
- 3 level volume control
- LED reversed polarity indicator
- Last number redial
- 10 number memory (15 digits max)
- High impact weather resistant housing and keypad
- Includes Test Leads with Angle Bed of Nails (ABN) clips and belt clip
- 3 year warranty



## **Ordering Information:**

3330      TeleTalker™ 330 Lineman's Test Set

# 8065 CamView HD Pro Ruggedized HD Camera Tester

*Powerful, portable, and designed with the technician in mind*

## Specifications

Analog and HD Video Testing	
Video Format	Auto recognizes NTSC/PAL, HD-CVI 3.0, HD-TVI 3.0, AHD 2.0
Test Pattern	Generates NTSC/PAL, HD-CVI, HD-TVI, or AHD test patterns (720P/1080P)
Signal Level	1vpp
Input/Output	Video IN BNC, Video OUT BNC
Digital Zoom	Supports 8-level portion view
Capture	Take snap shot or record video
Power Output	
Output	12V/1A power output to camera. Connector is 4mm diameter; pin is 1.6mm diameter
System	
Screen	4.0 inch TFT 800*RGB*480(WVGA) resolution, 16.7M color, backlight with adjustable brightness
Operation	Power key, 13 control keys
Language	User selectable -- English, French, Spanish, Russian, Chinese
Auto Shut-off	Disable / 5~60 minutes
Software	Supports online upgrade through USB using a Windows computer
Power	
Charger	12V/1A (5.5mm) power supply
Battery	Dedicated battery, user replaceable, 7.4V lithium-ion polymer battery, capacity 10.4Wh
Battery runtime	Approximately 5 hours
Power Saving	Auto power off; Real-time battery level indicator
Other	
Storage	8GB flash built in; use micro USB port to connect external device
LED Light	(2) 35lm LED lights
Dimensions	6.9 x 4.4 x 1.5" (175 x 113 x 37mm)
Weight	3.5lbs (1.6kg)