
## **ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-2-8-8**

APPROX WEIGHT: 276 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\* ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



Ρ

R

QUOTED LEAD TIME: X

## STANDARD FEATURES MODEL NUMBER IS AHA-2-8-8

SPECIAL FEATURES NONE

CAPACITY IS 2,000 LBS. BASE WIDTH IS 53 3/4" MAX OVERALL HEIGHT IS 104" I-BEAM HEIGHT IS 6" I-BEAM FLANGE WIDTH IS 3 5/16" OVERALL I-BEAM LENGTH IS 96" USABLE I-BEAM LENGTH IS 72 1/4" ADJUSTABLE UNDER I-BEAM HEIGHT

> 68" MIN 98" MAX

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS CASTERS: (4) Ø8" X 2" WIDE GLASS FILLED NYLON SWIVEL CASTERS WITH FOUR LOCKING POSITIONS

CRANE MAY BE TAKEN APART AND BUNDLED WITH (2) INCLUDED STRAPS FOR EASY TRANSPORT ALUMINÚM CONSTRUCTION

	MODIFIED ARE NON-RETURNABLE  [ ] As drawn [ ] As marked		
	L Signed:	Date:	
	Printed Name:_		
	LEAD TIME WILL STA	ART UPON RECEIPT OF SIGNED APPROVAL DRAWING	
DISTRIBUTOR'S NAME: P.O.# Y			
VESTIL MANUFACTURING W.O.# X			
DR	RAWN BY: ND	DATE: 02/01/2011 SALES: X	
RE	FERENCE: X	SCALE: 1:24 FILE NAME:	

QUOTE #

Χ

28-007-187

CONFIRM PRODUCT AND INSTALLATION

COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE

AND LOCAL REGULATIONS AND STANDARDS.

UNITS REQUIRING APPROVAL DRAWINGS OR