



PROTO®

Item # 33HE10
Mfr. Model # J47184

Set Includes:

Mfg Part #	Description	Qty
J4982	SET HEX KEY 7PC	1
J4983	SET HEX KEY 13PC LONG	1
J60002	BIT INSERT 1 PHIL 1/4HEX	1
J60008	BIT INSERT 2 PHIL 1/4HEX	1
J60020	BIT INSERT 3 PHIL 1/4HEX	1
J60200	BIT INSERT SLOT 1/4HEX 25	1
J60202	BIT INSERT SLOT 1/4HEX 25	1
J60204	BIT INSERT SLOT 1/4HEX 25	1
J60206	BIT INSERT SLOT 1/4HEX 25	1
J60208	BIT INSERT SLOT 1/4HEX 25	1
J60500	BIT INSERT T6 TORX 1/4HEX	1
J60502	BIT INSERT T7 TORX 1/4HEX	1
J60504	BIT INSERT T8 TORX 1/4HEX	1
J60506	BIT INSERT T9 TORX 1/4HEX	1
J60508	BIT INSERT T10 TORX 1/4HE	1
J60510	BIT INSERT T15 TORX 1/4HE	1
J60512	BIT INSERT T20 TORX 1/4HE	1
J60514	BIT INSERT T25 TORX 1/4HE	1
J60516	BIT INSERT T27 TORX 1/4HE	1
J60518	BIT INSERT T30 TORX 1/4HE	1
J60520	BIT INSERT T40 TORX 1/4HE	1
J60530	BIT INSERT T10 TORX T PRO	1
J60532	BIT INSERT T15 TORX T PRO	1
J60534	BIT INSERT T20 TORX T PRO	1
J60536	BIT INSERT T25 TORX T PRO	1
J60538	BIT INSERT T27 TORX T PRO	1
J9300MS	SCRWDR MAGNETIC BIT HOLDER	1
J3018	WRENCH OPEN END 1/4 X 5/16	1
J3020	WRENCH OPEN END 3/8 X 5/16	1
J3021	WRENCH OPEN END 3/8 X 7/16	1
J3025	WRENCH OPEN END 7/16 X 1/2	1
J3026	WRENCH OPEN END 1/2 X 9/16	1
J30809	WRENCH OPEN END 8MM X 9MM	1
J31011	WRENCH OPEN END 10MM X 11MM	1
J31213	WRENCH OPEN END 12MM X 13MM	1
J31415	WRENCH OPEN END 14MM X 15MM	1

Mfg Part #	Description	Qty
J47045TM	SOCKET 1/4DR 4.5MM 12PT	1
J4704M	SOCKET 1/4 DR 4MM 6 PT	1
J47055M	SOCKET 1/4 DR 5.5MM 6 PT	1
J4705LM	SOCKET 1/4 DR 5MM 6 PT DEEP	1
J4705M	SOCKET 1/4 DR 5MM 6 PT	1
J4705TM	SOCKET 1/4 DR 5MM 12 PT	1
J4706	SOCKET 1/4 DR 3/16 6 PT	1
J4706LM	SOCKET 1/4 DR 6MM 6 PT DEEP	1
J4706LT	SOCKET 1/4 DR 3/16 12 PT DEE	1
J4706M	SOCKET 1/4 DR 6MM 6 PT	1
J4706TM	SOCKET 1/4 DR 6MM 12 PT	1
J4707	SOCKET 1/4 DR 7/32 6 PT	1
J4707LM	SOCKET 1/4 DR 7MM 6 PT DEEP	1
J4707LT	SOCKET 1/4 DR 7/32 12 PT DEE	1
J4707M	SOCKET 1/4 DR 7MM 6 PT	1
J4707TM	SOCKET 1/4 DR 7MM 12 PT	1
J4708	SOCKET 1/4 DR 1/4 6 PT	1
J4708L	SOCKET 1/4 DR 1/4 6 PT DEEP	1
J4708LM	SOCKET 1/4 DR 8MM 6 PT DEEP	1
J4708LT	SOCKET 1/4 DR 1/4 12 PT DEEP	1
J4708M	SOCKET 1/4 DR 8MM 6 PT	1
J4708TM	SOCKET 1/4 DR 8MM 12 PT	1
J4709	SOCKET 1/4 DR 9/32 6 PT	1
J4709L	SOCKET 1/4 DR 9/32 6 PT DEEP	1
J4709LM	SOCKET 1/4 DR 9MM 6 PT DEEP	1
J4709LT	SOCKET 1/4 DR 9/32 12 PT DEE	1
J4709M	SOCKET 1/4 DR 9MM 6 PT	1
J4709TM	SOCKET 1/4 DR 9MM 12 PT	1
J4710	SOCKET 1/4 DR 5/16 6 PT	1
J4710L	SOCKET 1/4 DR 5/16 6 PT DEEP	1
J4710LM	SOCKET 1/4 DR 10MM 6 PT DEEP	1
J4710LT	SOCKET 1/4 DR 5/16 12 PT DEE	1
J4710M	SOCKET 1/4 DR 10MM 6 PT	1
J4710TM	SOCKET 1/4 DR 10MM 12 PT	1
J4711L	SOCKET 1/4 DR 11/32 6 PT DEEP	1
J4711LM	SOCKET 1/4 DR 11MM 6 PT DEEP	1

Mfg Part #	Description	Qty
J4711LT	SOCKET 1/4 DR 11/32 12 PT D	1
J4711M	SOCKET 1/4 DR 11MM 6 PT	1
J4711TM	SOCKET 1/4 DR 11MM 12 PT	1
J4712	SOCKET 1/4 DR 3/8 6 PT	1
J4712L	SOCKET 1/4 DR 3/8 6 PT DEEP	1
J4712LT	SOCKET 1/4 DR 3/8 12 PT DEEP	1
J4712M	SOCKET 1/4 DR 12MM 6 PT	1
J4712TM	SOCKET 1/4 DR 12MM 12 PT	1
J4713M	SOCKET 1/4 DR 13MM 6 PT	1
J4713TM	SOCKET 1/4 DR 13MM 12 PT	1
J4714	SOCKET 1/4 DR 7/16 6 PT	1
J4714L	SOCKET 1/4 DR 7/16 6 PT DEEP	1
J4714LT	SOCKET 1/4 DR 7/16 12 PT DEE	1
J4716	SOCKET 1/4 DR 1/2 6 PT	1
J4716LT	SOCKET 1/4 DR 1/2 12 PT DEEP	1
J4718	SOCKET 1/4 DR 9/16 6 PT	1
J5009M	SOCKET 3/8 DR 9MM 12 PT DEEP	1
J5010M	SOCKET 3/8 DR 10MM 12 PT DEE	1
J5010MH	SOCKET 3/8 DR 10MM 6 PT DEEP	1
J5011M	SOCKET 3/8 DR 11MM 12 PT DEE	1
J5011MH	SOCKET 3/8 DR 11MM 6 PT DEEP	1
J5012	SOCKET 3/8 DR 3/8 12 PT DEEP	1
J5012M	SOCKET 3/8 DR 12MM 12 PT DEE	1
J5012MH	SOCKET 3/8 DR 12MM 6 PT DEEP	1
J5013M	SOCKET 3/8 DR 13MM 12 PT DEE	1
J5013MH	SOCKET 3/8 DR 13MM 6 PT DEEP	1
J5014	SOCKET 3/8 DR 7/16 12 PT DEE	1
J5014M	SOCKET 3/8 DR 14MM 12 PT DEE	1
J5014MH	SOCKET 3/8 DR 14MM 6 PT DEEP	1
J5015M	SOCKET 3/8 DR 15MM 12 PT DEE	1
J5016	SOCKET 3/8 DR 1/2 12 PT DEEP	1
J5017M	SOCKET 3/8 DR 17MM 12 PT DEE	1
J5018	SOCKET 3/8 DR 9/16 12 PT DEE	1
J5018M	SOCKET 3/8 DR 18MM 12 PT DEE	1
J5020	SOCKET 3/8 DR 5/8 12 PT DEEP	1
J5209M	SOCKET 3/8 DR 9MM 12 PT	1
J5209MH	SOCKET 3/8 DR 9MM 6 PT	1
J5210	SOCKET 3/8 DR 5/16 12 PT	1
J5210H	SOCKET 3/8 DR 5/16 6 PT	1
J5210M	SOCKET 3/8 DR 10MM 12 PT	1
J5211	SOCKET 3/8DR 11/32 12PT	1
J5211M	SOCKET 3/8 DR 11MM 12 PT	1
J5211MH	SOCKET 3/8 DR 11MM 6 PT	1

Mfg Part #	Description	Qty
J5212	SOCKET 3/8 DR 3/8 12 PT	1
J5212H	SOCKET 3/8 DR 3/8 6 PT	1
J5212M	SOCKET 3/8 DR 12MM 12 PT	1
J5212MH	SOCKET 3/8 DR 12MM 6 PT	1
J5213M	SOCKET 3/8 DR 13MM 12 PT	1
J5213MH	SOCKET 3/8 DR 13MM 6 PT	1
J5214	SOCKET 3/8 DR 7/16 12 PT	1
J5214H	SOCKET 3/8 DR 7/16 6 PT	1
J5214M	SOCKET 3/8 DR 14MM 12 PT	1
J5214MH	SOCKET 3/8 DR 14MM 6 PT	1
J5215M	SOCKET 3/8 DR 15MM 12 PT	1
J5215MH	SOCKET 3/8 DR 15MM 6 PT	1
J5216	SOCKET 3/8 DR 1/2 12 PT	1
J5216H	SOCKET 3/8 DR 1/2 6 PT	1
J5216M	SOCKET 3/8 DR 16MM 12 PT	1
J5216MH	SOCKET 3/8 DR 16MM 6 PT	1
J5217	SOCKET 3/8DR 17/32 12PT	1
J5217M	SOCKET 3/8 DR 17MM 12 PT	1
J5217MH	SOCKET 3/8 DR 17MM 6 PT	1
J5218	SOCKET 3/8 DR 9/16 12 PT	1
J5218H	SOCKET 3/8 DR 9/16 6 PT	1
J5218M	SOCKET 3/8 DR 18MM 12 PT	1
J5219	SOCKET 3/8DR 19/32 12PT	1
J5220	SOCKET 3/8 DR 5/8 12 PT	1
J5220H	SOCKET 3/8 DR 5/8 6 PT	1
J5222	SOCKET 3/8 DR 11/16 12 PT	1
J5222H	SOCKET 3/8 DR 11/16 6 PT	1
J5224	SOCKET 3/8 DR 3/4 12 PT	1
J5224H	SOCKET 3/8 DR 3/4 6 PT	1
J5226H	SOCKET 3/8 DR 13/16 6 PT	1
J5228	SOCKET 3/8 DR 7/8 12 PT	1
J5228H	SOCKET 3/8 DR 7/8 6 PT	1
J5417M	SOCKET 1/2 DR 17MM 12 PT	1
J5418M	SOCKET 1/2 DR 18MM 12 PT	1
J5419M	SOCKET 1/2 DR 19MM 12 PT	1
J5421M	SOCKET 1/2 DR 21MM 12 PT	1
J5422M	SOCKET 1/2 DR 22MM 12 PT	1
J5424	SOCKET 1/2 DR 3/4 12 PT	1
J5426	SOCKET 1/2 DR 13/16 12 PT	1
J5428	SOCKET 1/2 DR 7/8 12 PT	1
J5430	SOCKET 1/2 DR 15/16 12 PT	1
J5432	SOCKET 1/2 DR 1 12 PT	1
J4749	RATCHET 1/4 DR	1

Mfg Part #	Description	Qty
J5249	RATCHET 3/8 DR	1
J4760	EXTENSION 1/4 DR 3	1
J5255	ADAPTER 3/8 F X 1/4 M	1
J5259	EXTENSION 3/8 DR 1-3/4	1
J5260	EXTENSION 3/8 DR 3	1
J5260-06	EXTENSION 3/8 DR 6	1
J5262	EXTENSION 3/8 DR 12	1
J5449	RATCHET 1/2 DR	1