



Nitrile

## Tough, durable protection in a black color to hide dirt, grease and stains

- Black color masks stains
- Textured fingertips provide a secure grip



### Industries

- Automotive
- Automotive Aftermarket
- Healthcare

### Recommended For

- Inspection, selecting, checking parts
- Inspection of parts, equipment
- Picking and fastening components
- Equipment repair and maintenance
- General Purpose Auto Aftermarket
- Use of cleaning tools and robotic equipment
- Tire rotation & changes
- Standard, moderate risk examination procedures
- Protection from Type I latex allergy in HCW's or patients



# MICROFLEX®

ADVANCED DISPOSABLE HAND PROTECTION

## Black Dragon® Zero BD-1000-NPF

Black Nitrile Exam Glove with Textured Fingertips

### TECHNICAL DATA SHEET

#### PRODUCT INFORMATION

Black Dragon® Zero BD-1000-NPF	
Material	Nitrile
Color	Black
Glove Design	Chlorinated, Powder-Free, Textured Fingers
Cuff	Beaded
Manufacturing/QMS Audit Standards	EN ISO 13485 : 2012
Regulatory/Standards Compliance	ASTM D6319, EN 420:2003 + A1:2009, FDA21 CFR 177-2600, US QSR/FDA 510(k) Medical Examination Grade
Packaging	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition
Country of Origin	Malaysia
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11)

#### PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767,EN420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.09 / 3.5		ASTM D3767,EN420
Finger Thickness (mm/mils)	0.14 / 5.5		ASTM D3767,EN420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	≥ 33	≥ 29	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
63000 Cyberjaya  
Selangor, Malaysia  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ahcenn PYC  
123610 Poccnr, Mockba  
Kpachonpechehckar  
Ha6. 12, n.3, op. 1304A  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.