



**SPYDER™**

 **NEW**

## SPYDER DOUBLE-SIDED OSCILLATING TOOL ATTACHMENTS

Make precise cuts and put the finishing touch on your job in a fraction of the time. Useful on almost any project, our double-sided oscillating tool attachments will quickly become the go-to items in your accessory toolbox.

### UNIVERSAL BLADES

These blades are great for cutting through virtually any material, including wood with nails, drywall, plastics, non-ferrous metals and fiberglass.



700000

#### ■ Universal Blade – Offset/Short

- › Double-sided, short offset blade for flush cuts
- › For use at any speed
- › Cutting width/depth: 1-3/4" (45 mm) x 1-3/8" (35 mm)
- › HSS – High Speed Steel
- › 18 TPI



7000001

#### ■ Universal Blade – Offset/Medium

- › Double-sided, medium offset blade for flush cuts
- › For use at medium/high speed
- › Cutting width/depth: 1-3/8" (35 mm) x 1-7/8" (48 mm)
- › HSS – High Speed Steel
- › 18 TPI



7000002

#### ■ Universal Blade – Offset/Wide Duo

- › Double-sided, dual use for multiple applications, wide offset blade for flush cuts
- › For use at medium/high speed
- › Cutting width/depth: 2-1/2" (65 mm) x 1-3/8" (35 mm)
- › HSS – High Speed Steel
- › 18 TPI

## JAPANESE BLADE

Our Japanese blade makes fast cuts in all types of wood, drywall and plastics with extremely close tolerances. The blade's thin kerf means you cut faster with less effort. Not for use with metal.



710000

### ■ Japanese Blade – Offset/Short

- › Double-sided, short offset blade for flush cuts
- › For use at any speed
- › Cutting width/depth: 1-3/4" (45 mm) x 1-3/8" (35 mm)
- › HCS – High Carbon Steel
- › 14 TPI

---

## SCRAPERS

Our rigid scraper is best for harder materials such as vinyl flooring, carpeting, adhesives, caulking and peeling paint. Our flexible scraper makes quick work of softer materials, including silicone joints, soft compounds and stickers.



720000

### ■ Scraper – Offset/Rigid

- › Double-sided, offset for flush scraping, rigid for hard materials
- › For use at any speed
- › Cutting width/depth: 1-3/4" (45 mm) x 1-3/8" (35 mm)
- › SS – Stainless Steel



720001

### ■ Scraper – Flexible

- › Double-sided, flat for long reach, flexible for soft materials
- › For use at any speed
- › Cutting width/depth: 1-3/4" (45 mm) x 2-1/4" (58 mm)
- › SS – Stainless Steel