

5/16"

JB INDUSTRIES

MSKIT2

MINI SPLIT TOOL KIT

**EVERYTHING YOU NEED FOR R410-A DUCTLESS MINI-SPLITS
IN ONE CONVENIENT KIT**



JB TOOL BAG PART# MSKIT1-BAG

- 20 Pockets to hold the tools you need to get the job done
- Rubber feet to prevent sliding
- Made of sturdy nylon fabric



PATRIOT BRASS MANIFOLD PART# 22500

- 2 1/2" Gauges - 410A only
- Surge dampened gauges for reduced needle movement
- Replaceable hose holder fittings
- 360° Swiveling hose holders



60" KOBRA HOSE SET PART# CCLS5-60

- UL approved for 410A
- Low loss fittings
- 3-point contact on depressor
- 5/16" red & blue hoses
- 1/4" yellow hose



RATCHETING FLARE TOOL PART# T30600

- Internal clutch prevents over-torquing
- Eccentric cone flaring for tubes with an OD of: 3/16", 1/4", 5/16", 3/8", 1/2", 5/8" & 3/4"



TORQUE WRENCH KIT PART# TRQ1080

- 7.375 - 59.004 Pound-Feet (10-80 N-M)
- 6-spanner heads (17, 22, 24, 26, 27 & 29mm)
- 1/2" DR ratchet head



HEX KEY SET PART# T30605

- Hex key set for Metric (2-8mm) & Imperial (5/64 - 1/4")



VALVE CORE REMOVER PART# A32535N

- 5/16" Female x 5/16" SAE Male
- 1/4" Side port
- Valve core can be removed & replaced without losing system charge



5/16" SHIELD REFRIGERANT LOCKING CAPS PART# SHLD-E4

- Provide your customers with protection against theft & huffing
- Pink rubber water-resistant sleeves
- 1 Tamper resistant bit included



5/16" BRASS CAPS PART# NFT5-5

- Finger tight sealing for all 5/16" SAE male connections



5 INCLUDED



BRASS ADAPTER PART# A31665

- 1/4" Female x 5/16" SAE Male



2 INCLUDED



JB is donating \$1 of this purchase to Operation Homefront



CONNECT WITH US
Visit us at www.jbind.com

JBIND.COM

800.323.0811

SALES@JBIND.COM

