



**MCR
SAFETY**

**9699
UltraTech
Dipped
Specification Sheet**

PRODUCT DESCRIPTION:

UltraTech® provides Ultra comfort, Ultra fit, and Ultra protection! The seamless nylon shell offers outstanding breathability and comfort while the HPT palm and finger coating provides grip, puncture resistance, abrasion resistance and dexterity.

FEATURES:

- Great tactile sensitivity
- Excellent comfort and fit
- Excellent grip
- Great dexterity
- CE SCORE 4131

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling, Assembly Line Production, Construction, Manufacturing, Plumbing



TECHNICAL DATA FOR: 9699

Series	UltraTech	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	3
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	15 Gauge		
Material	Nylon		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9699
UltraTech
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9699L	Large	10.44	5.88	N/A	20.916 lb.	1.743
9699M	Medium	10.04	5.20	N/A	18.912 lb.	1.576
9699S	Small	9.64	4.72	N/A	18.372 lb.	1.531
9699XL	X - Large	10.82	6.180	N/A	22.980 lb.	1.915
9699XS	X - Small	9.25	4.44	N/A	16.980 lb.	1.415
9699XXL	XX - Large	11.22	6.53	N/A	24.096 lb.	2.008

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved