



MCR
SAFETY

6015

NitriShield

Disposable

Specification Sheet

PRODUCT DESCRIPTION:

Nitrile contain no latex proteins and offer excellent resistance to punctures and tears. Nitrile gloves are three times more puncture resistant than rubber and can be used to offer superior resistance to many types of chemicals. This glove is an excellent alternative for individuals who experience allergic reactions to latex. The 6015 is a industrial / food service grade powder free nitrile glove that measures 4 mil in thickness and is 9.5 inches in length.

FEATURES:

- 4 mil, Blue Powder Free Nitrile
- Component materials comply with all federal regulations for food contact
- Rolled Cuff
- Textured Grip
- 9.5 Inch Length

APPLICATIONS:

Janitorial , Nursing Home Care, Painting, Food service, Canning



TECHNICAL DATA FOR: 6015

Series	NitriShield	Overall Length	9.5 in.
Material Group	Unsupported		
Product Type	Disposable		
Glove Size	Large		
Material	Nitrile		
Grade	Premium		
Features	Reversible		
Lining	Unlined		
Pattern	Reversible		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

6015

NitriShield

Disposable

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6015L	Large	9.646	4.803	N/A	15.872 lb.	15.872
6015M	Medium	9.567	4.645	N/A	15.393 lb.	15.393
6015S	Small	9.212	4.253	N/A	14.320 lb.	14.320
6015XL	X - Large	9.724	5.276	N/A	17.380 lb.	17.380
6015XXL	XX - Large	10.078	5.551	N/A	18.273 lb.	18.273

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved