

PC 589

Shurtape®
TRUE TO YOUR WORK™

SHURGRIP® LIGHT DUTY, CO-EXTRUDED DUCT TAPE

TYPICAL APPLICATIONS

- For light duty sealing, seaming, repairing, holding and waterproofing applications that require aggressive stick and superior hold
- For temporary or permanent use

PRODUCT FEATURES

- Improved holding power to poly-sheeting and steel
- Consistent, low-force unwind off the roll
- Hand-tearable in machine and cross directions
- Made using Polybonded CO-EX Technology®

CONSTRUCTION

Overall Grade/Function: Light duty

Backing: Waterproof polyethylene film with a cloth carrier

Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

APPLICABLE STANDARDS

Tested in accordance with UL 723; FSI 0/SDI 0; US Green Building Council – LEED® Point Contributor Product

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES STANDARD METRIC

Tensile Strength	18 lbs/in width	31.5 N/10 mm
Adhesion to Stainless Steel	106 oz/in width	11.60 N/10 mm
Thickness	7 mils	0.18 mm
Elongation	21%	21%
Service Temperature Range	40 F to 200 F	4 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

