

FMLWL LED Wraparound

Multipurpose Linear Ambient Lighting

The FMLWL LED Wraparound by Lithonia Lighting® provides efficient and economical ambient lighting in surface-mount applications. The stylish, low-profile linear wrap delivers up to 50,000 hours of energy-saving LED lighting with widespread, even illumination. With simplified installation and a durable polycarbonate lens, the versatile FMLWL is perfect for a wide variety of residential, commercial and institutional applications.

Key Features and Benefits:





- Available in 2-foot and 4-foot versions for application versatility
- Equivalent light output to traditional 2-lamp T8 wraparounds in a sleek, modern design
- Multi-volt, higher lumen versions are optimized for commercial applications, provide 0-10V dimming capability and are DesignLights Consortium (DLC) qualified products
- Suitable for use in damp locations such as laundry rooms and stairwells
- Contractor Select™ options for the most popular and readily available configurations



FMLWL LED Wraparound



Ordering Information

Description	Model	CI Code	UPC Code	Wattage	Pallet Quantity	Contractor Select
2' FMLWL, 1400 Lumens, 4000K	FMLWL 24 840	*226LWP	00888791197921	20W	224	
2' FMLWL, 3000 Lumens, 3500K	FMLWL 24 835 ZT MVOLT	*250LW2	00191848384701	32W	224	
2' FMLWL, 3000 Lumens, 4000K	FMLWL 24 840 ZT MVOLT	*250LW1	00191848384657	32W	224	
4' FMLWL, 2900 Lumens, 4000K	FMLWL 48 840	*226LWW	00888791197969	40W	112	
4' FMLWL, 4600 Lumens, 3500K	FMLWL 48 835 ZT MVOLT	*250LVP	00191848384565	48W	112	
4' FMLWL, 4600 Lumens, 4000K	FMLWL 48 840 ZT MVOLT	*250LVM	00191848384558	48W	112	



DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org/QPL to confirm which versions are qualified.

Visit www.lithonia.com for more information.