


Item	Parts No.	Description	Qty
3	P091585	Spring-Valve	2
4	P091584	Cap-O-Ring	2
5	P091582	Valve-Throttle	1
7	<u>P083076</u>	O-Ring	2
13	P091583	Valve-Blower	1
14	475353	Lever-Assembly	1
	P084042	Lever-Throttle (Blower Type)	1
15	P084043	Pin-Lever	1
19	P009876	Plug-Valve	2
22	P084037	Shim (.005 in.)	As
	P084038	Shim (.010 in.)	Requ'd
23	P043309	Lid	1
24	P043310	Valve-Cycling (Metalic)	1
	P119294	Valve-Cycling (Rubber)(Not Shown)	1
26	P084034	Case-Valve Cycling	1
32	P109273	Head-Cylinder	1
	P113310	Head-Cylinder (Blower Type)	1
58	P113312	Cylinder (Incl: Index No. 65)	1
59	P109271	Locknut-Cylinder	1
61	<u>P084033</u>	Piston	1
65	P041557	Sleeve-Cylinder	1
68	P088815	Lock-Rubber	1
69	P050933	Sleeve-Chisel (1/2" Q.O.)	1
71	P088813	Ring-Chisel Lock	1

Item	Parts No.	Description	Qty
74	P070416	Ball-Steel (5/16")	1
76	P050934	Ring-Retaining (External)(#5160-98)	1
160	P117630	Housing (Round Nose)	1
	P117631	Housing (Rectangular Nose)	1
161	P117633	Screw-Soc. Hd. (#10-32 x 1 1/4")	2
162	P100150	Spring-Compression	1
163	<u>P100964</u>	Buffer-Holder	2
164	P100145	Holder-Needle	1
165	<u>P100146</u>	Set-Needle (7 in.)(Consists of 19 Steel Needles)	1
	<u>P106454</u>	Set-Needle (7 in.)(Consists of 19 Stainless Steel Needles)	1
	<u>P106455</u>	Set-Needle (7 in.)(Consists of 19 Beryllium Copper Needles)	1
166	P117632	Clamp-Housing	1
167	P100144	Anvil	1

	P122303	Operator's Manual
	CA144007	Decal-Safety Warning
	6159948780	Safety Instruction