

SAWHORSE SCAFFOLD

SERIES L-2032

ALUMINUM

TYPE IA

300 LBS
LOAD CAPACITY

(Includes weight of user plus materials)

SMALL SIZES CAN HANDLE BIG JOBS

Step on up to the extra wide top with slip-resistant tread, giving you plenty of room to work on. Need a scaffold so you can move from one side to the other? Simply put down a scaffold grade wood or metal plank between the two and walk across. Put a large flat sheet of board down and now you have a table top work station. Designed with a gap in the center of this top for easy handling, this sawhorse is built to move around your jobsite.

EXTRA WIDE WORK SURFACE ALLOWS YOU TO STAND ON THE TOP



GRAB AND GO GAP IN CENTER OF WORK SURFACE TO PICK UP AND MOVE WHERE YOU NEED IT



LOUISVILLE
LADDER

BECAUSE WORK AIN'T PLAY.



ANSI
Standard for portable ladders
of American National Standards Institute
ANSI A10.8



SAWHORSE SCAFFOLD



SERIES L-2032



1 Heavy Duty Top
10-in deep top with slip-resistant tread



2 Steel Hinges
Heavy-gauge steel hinges



3 Spreader Brace
Heavy duty pinch-resistant spreader braces



4 Heavy Duty Gusset
Heavy-duty gusset on every step for increased rigidity and support



5 Aluminum Shoe
Slip-resistant rubber tread with heavy duty aluminum shoe



MODEL	SIZE	BOTTOM WIDTH (IN)	APPROX. SPREAD (IN)	MAX. STANDING HEIGHT (FT)	MAX REACH (FT)	APPROX. WT. (LBS)	VOLUME
L-2032-02	2'	32	26	1' 10"	8' 5"	13	5
L-2032-03	3'	33 3/8	34	2' 9"	9' 4"	19	7.7
L-2032-04	4'	34 3/4	43	3' 9"	10' 4"	25	10.5



LOUISVILLELADDER.COM

1.800.666.2811