




METALLIC LOW PROFILE WIU COVERS

**Single Gang Metal Low Profile While-In-Use Covers - Extra Duty®
Horizontal 8-in-1**

C11



Catalog #: MX4380S

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use.
N/A

PRODUCT FEATURES

- Revolutionary patented design expands from 2" to 3-1/2" for while-in-use needs
- Heavy duty die-cast metal construction
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Includes attached gasket and mounting hardware
- Lockable tab
- Premium Powder Coat

UL LISTED

File E212332

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A & B) Extra Duty Rated

US PATENTS

8,314,334; 8,259,253 B1; 6,420,654; 8,106,295 B1

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Gangs: 1

PRODUCT MEASUREMENTS

Depth: 2 in. to 3-1/2 in.
Wt. Ea. (Lbs.): 0.825

PACKAGING

Package Type: Shrink
 Std. Pkg.: 3
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 82.50
 Ship Carton Length (in.): 9.75
 Ship Carton Width (in.): 5.88
 Ship Carton Height (in.): 6.13
 Ctn Weight (Lbs.): 3.30
 Pallet Qty: 768.00
 UPC Number: 092326101349
 I2of5: 30092326101340