

# Carpenters' Pincers

DIN ISO 9243

50

- > heavy-duty
- > preferred by tradespeople
- > wear-resistant
- > cutting edge hardness (approx. 60 HRC)
- > special tool steel; forged, oil-hardened



50 00 210



50 01 225



| Product Number | Packaging | ↔<br>Inch<br>mm | Pliers               | Head     | Handles            | Cutting capacities  |          |
|----------------|-----------|-----------------|----------------------|----------|--------------------|---------------------|----------|
|                |           |                 |                      |          |                    | ●<br>Ø Inch<br>Ø mm | ⚖<br>lbs |
| 50 00 160      |           | 6 1/4<br>160    | ✔ black atramentized | polished | black atramentized | 5/64<br>1.8         | 0.49     |
| 50 00 180      |           | 7<br>180        |                      |          |                    | 5/64<br>2.0         | 0.70     |
| 50 00 210      |           | 8 1/4<br>210    |                      |          |                    | 3/32<br>2.2         | 0.94     |
| 50 00 250      |           | 10<br>250       |                      |          |                    | 3/32<br>2.2         | 1.27     |
| 50 00 300      |           | 12<br>300       |                      |          |                    | 3/32<br>2.4         | 1.87     |
| 50 01 160      |           | 6 1/4<br>160    | ✔ black atramentized | polished | plastic coated     | 5/64<br>1.8         | 0.53     |
| 50 01 180      |           | 7 1/4<br>180    |                      |          |                    | 5/64<br>2.0         | 0.73     |
| 50 01 210      |           | 8 1/4<br>210    |                      |          |                    | 3/32<br>2.2         | 0.98     |
| 50 01 225      |           | 9<br>225        |                      |          |                    | 3/32<br>2.2         | 1.34     |
| 50 01 250      |           | 10<br>250       |                      |          |                    | 3/32<br>2.2         | 1.29     |
| 50 01 300      |           | 12<br>300       |                      |          |                    | 3/32<br>2.4         | 1.99     |