

PROTAC HL® USB

USB RECHARGEABLE, HIGH LUMEN TACTICAL LIGHT

USB rechargeable, high lumen tactical light features multi-fuel design. It accepts multiple battery sources to use as a back up so you'll always have power when you need it.



TEN-TAP® Programming: Choice of three operating modes: 1.) high/strobe/low; 2.) high only; 3.) low/medium/high



- High: 1,000 lumens; 219m beam; runs 1.5 hours
- Medium: 380 lumens; 133m beam; runs 3.5 hours
- Low: 65 lumens; 53m beam; runs 23 hours
- Strobe: runs 1.5 hours

LED Solid State power regulation provides maximum light output throughout battery life

Removable pocket clip

IPX4 water-resistant; 1m impact resistance tested

6.50" (16.5 cm); 7.2 oz (204g) with Li-Ion rechargeable battery (included)

Limited Lifetime Warranty
Visit streamlight.com for full warranty information

#88052 - ProTac HL USB - with USB cord

#88091 - ProTac HL USB - 230V AC/12V DC

#88054 - ProTac HL USB - 120V AC/12V DC

#88055 - ProTac HL USB - 240V AC/12V DC