

### 316 STAINLESS STEEL TUBING - COILED

- Welded
- -325 to 1500 Deg F
- 50 Feet Long
- Meets ASTM 269

<b>Grainger Stock No.</b>	<b>Manufacturer Model No.</b>	<b>Inside Dia (In)</b>	<b>Outside Dia (In)</b>	<b>Wall Thickness (In)</b>	<b>Outside Dia Tolerance</b>	<b>Max Pressure</b>
3ADJ7	18256	.085	1/8	.020	+.005"/- 0.005"	4904 PSI At 72 Deg F
3ADJ8	18258	.210	1/4	.020	+.005"/- 0.005"	2500 PSI At 72 Deg F
3ADJ9	18260	.194	1/4	.028	+.005"/- 0.005"	3570PSI At 72 Deg F
3ADK1	18265	.335	3/8	.020	+.005"/- 0.005"	1678 PSI At 72 Deg F
3ADK2	18267	.319	3/8	.028	+.005"/- 0.005"	2380 PSI At 72 Deg F
3ADK3	18269	.460	1/2	.020	+.020"/- 0.020"	1337 PSI At 72 Deg F