


M-5440 1



- NOTES:
1. WIRE CAPACITY: #16 AWG TO #12 AWG COPPER WIRE ONLY.
  2. CORD RANGE: Ø .32" TO .66", TYPE SJ, SJU, S OR SO.
  3. ALL DIMS. TO BE INCHES.  
[mm]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BASE	BAKELITE	BLACK
BLADE HOLDER	BAKELITE	GRAY
CONTACT BLADES	.075 BRASS	
CONTACT ENDS	.185 BRASS WIRE	
BINDING SCREWS	BRASS	1-WHITE
HEX HD. BINDING SC.	BRASS	GREEN
GR. SHUNT	.015 BRONZE	
BUSHING	RUBBER	
COVER	.062 ALUM.	SEMI-BRIGHT
CORD RETAIN. COVER	.093 ST. ST.	
EPOXY KIT	(NOT SHOWN)	

DIMENSION SHEET FOR CAT. NO. HBL23004HG  
 REPAIRABLE  NON-REPAIRABLE

SYM	REVISIONS	APP	DATE
1	ADDED NOTES 1 THRU 3; CAT. NO "HBL23004HG" WAS "23004-HG"; CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	2/5/05

**B**  
**M-5440**

**TITLE**  
 20A 125VAC, 3 WIRE  
 HOSPITAL GENERAL USE  
 HUBBELLOCK GROUNDING PLUG  
 WITH CORD GRIP

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
FRACTIONS ± 1/64		BRIDGEPORT, CONN.	
DECIMALS ± .005		DR. BY <u>ASM</u>	APP. BY _____
ANGLES ± 2°		TR. BY _____	SCALE <u>1=1</u>
		CHK'D BY _____	DATE <u>2-10-72</u>