Hubbellock® Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hubbellock® Plug

HUBBELL

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Ordering Information

Description Nylon housing, thermoset interior	Cord Diameter .320"- .660"(8.12-16.5)	UPC 783585017389	Catalog Number HBL23005GB	



Specifications

Device Color	Black/White
Housing	Nylon
Cord Clamp Material	Nylon
Plug Housing	Thermoset
Contacts	Brass
Assembly Screws	Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage

2,000V minimum

Mechanical


Terminal Accommodation #16 AWG - #12 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better Moisture Resistance IP30 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Accessories

Connector	HBL23002GB
Single Receptacle	HBL2300G

Resources

Customer Use Drawing eCatalog

