



M-5437 2



NOTES:

1. WIRE CAPACITY: #8AWG TO #4AWG COPPER WIRE ONLY.
2. CORD RANGE: Ø .83 TO 1.30, TYPE "S" OR "SO".  
[21.1] [33.0]
3. ALL DIMS. TO BE INCHES.  
[mm]

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
INSULATOR	DUREZ	BLACK
CONTACTS	BRASS	
CLAMPS	ALUMINUM	1-GREEN
CLAMP SCREWS	STEEL	ZINC PL.
GR. SHUNT	.051 BRASS	
CENTER POST	STEEL	ZINC PL.
COVER	.062 STEEL	WHITE
RETAINER COVER	LEXAN	GRAY
BUSHING	RUBBER	
CORD CLAMPS	.078 CRS	YELLOW NYLON COATING
REDUCERS	RUBBER	

DIMENSION SHEET FOR CAT. NO. HBL25525

REPAIRABLE  NON-REPAIRABLE

B

M-5437

2

SYM	REVISIONS	APP	DATE
2	ADDED NOTES 1 THRU 3; REVISED TITLE; REMOVED "RUBBER GRIP" & "CORD CLAMP" CALLOUTS; "HBL25525" WAS "25525"; CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	2/5/05
1	SPEC'S REVISED	hbd	9-20-72

**TITLE**  
50A 250VAC, 2 POLE, 3 WIRE  
MOBILE X-RAY HUBBELLOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED  
FRACTIONS ± 1/64  
DECIMALS ± .005  
ANGLES ± 2°

**HARVEY HUBBELL, INC.**  
BRIDGEPORT, CONN.

DR. BY A.S.M. APP. BY \_\_\_\_\_  
TR. BY \_\_\_\_\_ SCALE (1:1)  
CHK'D BY \_\_\_\_\_ DATE 2-9-72