



M-4435 7



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
INSULATORS	DUREZ	BLACK
BUSHING	RUBBER	
RETAINER COVER	POLY CARBONATE	BLUE
COVER	.062 STEEL	ZINC PL.
CORD CLAMPS	.078 C.R.S.	YEL NYLON COATING
CONTACTS	BRASS	
CLAMPS	ALUMINUM	WHITE
CLAMP SCREWS	STEEL	ZINC PL.
GROUND CLAMP	.050 C.R.S.	ZINC PL.
CENTER POST	STEEL	ZINC PL.

DIMENSION SHEET FOR CAT. NO. HBL26519

REPAIRABLE  NON-REPAIRABLE

B M-4435

7

SYM	REVISIONS	APP	DATE
7	ADDED NOTES 1 THRU 3; "HBL26519" WAS "26519"; REVISED TITLE; REMOVED "CORD GRIP" & "RUBBER GRIP" CALL-OUTS; CONVERTED ALL DIMS. TO DECIMAL/METRIC PER DCN 11902 RCM	JPP	1/27/05

- NOTES:
1. WIRE CAPACITY: #8/5 AWG - #4/5 AWG COPPER WIRE ONLY.
  2. CORD RANGE: Ø 1.00 TO 1.45, TYPE "S" OR "SO".  
[25.4] [36.8]
  3. ALL DIMENSIONS TO BE INCHES.  
[mm]

TITLE  
60A 600VAC, 4 POLE, 5 WIRE  
GROUNDING HUBBELLOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
		BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY <u>DJR</u>	APP. BY	
DECIMALS ± .005	TR. BY	SCALE <u>FULL</u>	
ANGLES ± 2°	CHK'D BY <u>J.C.H.</u>	DATE <u>3-8-66</u>	