


# Twist-Lock® Devices


## Non-NEMA 30 Amp, 250, 125/250 Volts and 3ØY 120/208 Volts AC 2 Pole, 3 Wire, Grounding and 3 Pole, 3 Wire, Non-Grounding

For Replacement Use Only

**IP20**  
SUITABILITY



**30A 250V**  
Non-NEMA  
Not UL listed



**30A 125/250V**  
Non-NEMA  
Not UL Listed

### Insulgrip® Plugs

| Description            | Cord Dia.             | Catalog Number                   |
|------------------------|-----------------------|----------------------------------|
| Black and white nylon. | .360"-.930"<br>(9-24) | <b>HBL3331GC</b> <b>HBL3331C</b> |

Note: See page B-54 for accessories.



**HBL3331GC**

### Insulgrip® Flanged Inlets

| Description               | Catalog Number    |
|---------------------------|-------------------|
| Nylon casing, back wired. | - <b>HBL3334C</b> |


Note: See page B-54 for accessories.



**HBL3334C**

For Replacement Use Only

**IP20**  
SUITABILITY



**30A 3Ø 250V AC**  
Non-NEMA  
Not UL Listed



Non-NEMA  
**30A 3Ø Y**  
**120/208V AC**  
Not UL Listed

### Insulgrip® Plugs

| Description            | Cord Dia.              | Catalog Number                    |
|------------------------|------------------------|-----------------------------------|
| Black and white nylon. | .350"-1.150"<br>(9-29) | <b>HBL3431GCB</b> <b>HBL3431C</b> |

Note: See page B-54 for accessories.

The devices shown on this page are not listed by Underwriters Laboratories Inc. and are for replacement use only in existing installations.



**HBL3431C**

**CAUTION:** To avoid electrical shock, review premises carefully and do not use if slot or blade configuration (design) is already in a circuit having a rating differing from the rating of this device.

Dimensions in Inches (mm)