Twist-Lock® Devices 30A, 3 Phase Y 277/480V AC, 4 Pole, 5 Wire Grounding

Insulgrip® Flanged Inlet

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Ordering Information

| Description | Device Color | UPC | Catalog Number |
|--------------------|--------------|--------------|----------------|
| Nylon casing, back | White | 783585039718 | HBL2825 |
| wired. | | | |

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing / Flange Nylon

Terminal Retainer Clear polycarbonate

Blades Brass

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel – nickel plated

Assembly Screws Steel - nickel plated Mounting Screw Nickel plated brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 500

Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17


Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C. Minimum -40°C (w/o impact)

HUBBELL







Accessories

| Connector | HBL2823 |
|-------------------------|---------|
| Weatherproof Lift Cover | WP2 |

Resources

Customer Use Drawing eCatalog

