# Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding HBL® Extra Heavy Duty Compact Duplex Receptacle



- Slender/compact design
- Brass Mounting Strap
- Triple wipe contacts

# **Ordering Information**

Description	Device Color	UPC	Catalog Number
Back and side wired	Black	783585434865	HBL5252BK

#### Listings

UL Listed to UL498 File No. E2186 Certified to CSA 22.2, No. 42 File 285 Fed. Spec. W-C596G NEMA® WD-6 Compliant

# **Specifications**

•	
Face	Nylon
Base	RTP
Contacts	Brass
Wire Clamp	Plated brass
Terminal Screws	Brass
Mounting Strap	.031" (.8) Brass
Automatic Self-grounding Clip	Stainless steel
Mounting Screws	Steel-Zinc Plated

# Performance

#### Electrical

Current Interrupting **Dielectric Voltage** 

Certified for current interrupting at full rated current Withstands 2,000V minimum

#### Mechanical

Product Identification Terminal Accommodation **Terminal Identification** 


Environmental

Flammability Operating Temperatures

Ratings are a permanent part of the device #14-#10 AWG copper stranded or solid conductor only Terminals identified in accordance with UL 498 and CSA

UL 94 V-0 Maximum continuous 75°C; minimum -40°C (w/o impact)





# Accessories

Wallplate or Weatherproof Cover Duplex Opening

#### Resources

Customer Use Drawing eCatalog



